

## Aspire Adjustable 2 Pressure Reducing Chair



The Aspire Adjustable 2 Pressure Reducing Day Chair has evolved with a stylish new look to fit all types of living areas. The new chair is designed to deliver exceptional comfort, configurability, and safety across a wide range of care environments. Built with a robust steel frame and industry-leading adjustability, it is an ideal solution for facilities requiring pressure seating that can be adjusted to suit diverse user needs.



- **High-SWL Steel Frame:** Robust steel frame achieves a Safe Working Load (SWL) of 200kg, a significant increase from the previous model at 160kg, making it ideal for heavy-duty and long-term care environments.
- **Pressure Injury Prevention:** Supportive memory foam and four-way PU stretch fabric assists with immersion and pressure redistribution during extended use.
- **Optimised Postural Support:** Contoured cushioning combined with adjustable head, seat, and back support promotes proper alignment and sustained comfort.
- **Exceptional Adjustability:** Fully adjustable seat width, depth, and height to accommodate varied body shapes, sizes and postural needs.
- **Tool-free Adjustment Points:** Ensure quick configuration for multiple users.
- **Integrated Spring-pin Safety System:** Prevents overextension and maintains secure, controlled adjustments.
- **Multi-layered Commercial-grade Foam:** Enhances longevity and sitting comfort.
- **Mobility-ready Rear Castors:** Helps transport the chair between rooms.

### Warranty Information

- 1 Year

| Code      | Display Name                                           | Total Width | Total Height  | Safe Working Load | Colour   | Seat Depth  | Seat Width  | Seat To Floor Height | Seat To Footrest | Backrest Height |
|-----------|--------------------------------------------------------|-------------|---------------|-------------------|----------|-------------|-------------|----------------------|------------------|-----------------|
| CHP208040 | Aspire Adjustable 2 Pressure Reducing Chair - Ash Grey | 690 - 790mm | 1160 - 1260mm | 200kg             | Ash Grey | 400 - 570mm | 500 - 600mm | 460 - 570mm          | 460 - 570mm      | 800mm           |